



EK082



Adjustable ambient probe

Technical properties

Compatibility

Compatible with EK187/ EG502

Resistance

Characteristic resistance value at 25 °C 11580 Ω

Connection

Sensor cable length max. 50 m

Probe conductor cross-section (recommended) 1.5 mm²

Settings

Temperature calibration, adjustable ± 3 °C

Equipment

Probe type fixed room sensor

Safety

Protection index IP IP30

Use conditions

Operating temperature 0...80 °C