



EK083

IP54

Universal probe

Technical properties

Compatibility

Compatible with EK186 / EK285 / EG502

Length

Maximum connection distance between receiver and transmitter 50m

Resistance

Characteristic resistance value at 25 °C 10 k Ω

Connection

Sensor cable length 4 m

Probe conductor cross-section (recommended) 1.5 mm²

Cable

Length of the connecting cable 4 m

Equipment

Probe type universal probe

Safety

Protection index IP IP54

REACH conform Yes

RoHS conform Yes

Use conditions

Operating temperature -30...90 °C

Instructions

Information text

Note: A 1500 Ω -resistor in connection in series is to be used in conjunction with the thermostat multifunction RMD (order no. EK187).