




EN146



Technical properties

Configuration

Number of modules	1
-------------------	---

Main electrical features

Rated operational voltage Ue	250 V
Frequency	50/60 Hz

Voltage

Rated insulation voltage	250 V
Command voltage AC	230 V

Electric current

Rated current	5 A
---------------	-----

Dimensions

Depth of installed product	58 mm
Height of installed product	85 mm
Width of installed product	17.5 mm

Power

Inrush power absorbed	5 VA
Operating consumption	5 VA
Total power loss under IN	2 W

Connection

Number of contacts	1
Type of contacts	1 changeover
Connection cross-section of the control cable solid	1 / 6 mm ²