



EPN050



### Auxiliary contact for centralised control

#### Technical properties

##### Configuration

Number of modules	0.5
-------------------	-----

##### Main electrical features

Rated operational voltage $U_e$	110 / 230 V
Frequency	50 Hz

##### Voltage

Command voltage AC	110 / 230 V
--------------------	-------------

##### Electric current

Rated current	1 A
---------------	-----

##### Dimensions

Depth of installed product	58 mm
Height of installed product	85 mm
Width of installed product	8.9 mm

##### Power

Total power loss under IN	0.1 W
---------------------------	-------

##### Connection

Connection cross-sect. flexible conductor	1 / 6mm <sup>2</sup>
Connection cross-sect. rigid cable	1,5 / 10mm <sup>2</sup>

##### Standards

European directive WEEE	concerned
-------------------------	-----------

##### Safety

REACH conform	No
RoHS conform	Yes
Halogen free	No

##### Use conditions

Operating temperature	-5...40 °C
Storage/transport temperature	-40...80 °C