




EPN051



Auxiliary contact 1NC+1NO

Technical properties

Configuration

Number of modules	0.5
-------------------	-----

Main electrical features

Rated operational voltage U_e	250 V
---------------------------------	-------

Voltage

Rated insulation voltage	250 V
--------------------------	-------

Electric current

Rated current	2 A
---------------	-----

Dimensions

Depth of installed product	58 mm
Height of installed product	83 mm
Width of installed product	8.75 mm

Power

Total power loss under IN	0.1 W
---------------------------	-------

Installation, mounting

Factory fitted	No
----------------	----

Connection

Connection cross-sect. flexible conductor	1 / 6mm ²
Connection cross-sect. rigid cable	1,5 / 10mm ²
Number of contacts	2
Type of contacts	1NC+1NO

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	No

Use conditions

Operating temperature	-5...40 °C
Storage/transport temperature	-40...80 °C