



EPN051



## Auxiliary contact 1NC+1NO

### Technical properties

#### Configuration

Number of modules	0.5
-------------------	-----

#### Main electrical features

Rated operational voltage $U_e$	250 V
---------------------------------	-------

#### Voltage

Rated insulation voltage	250 V
--------------------------	-------

#### Electric current

Rated current	2 A
---------------	-----

#### Dimensions

Depth of installed product	58 mm
----------------------------	-------

Height of installed product	83 mm
-----------------------------	-------

Width of installed product	8.75 mm
----------------------------	---------

#### Power

Total power loss under IN	0.1 W
---------------------------	-------

#### Installation, mounting

Factory fitted	No
----------------	----

#### Connection

Connection cross-sect. flexible conductor	1 / 6mm <sup>2</sup>
---	----------------------

Connection cross-sect. rigid cable	1,5 / 10mm <sup>2</sup>
------------------------------------	-------------------------

Number of contacts	2
--------------------	---

Type of contacts	1NC+1NO
------------------	---------

Type of connection	with screw
--------------------	------------

#### Standards

European directive WEEE	concerned
-------------------------	-----------

#### Use conditions

Operating temperature	-5...40 °C
-----------------------	------------

Storage/transport temperature	-40...80 °C
-------------------------------	-------------