



EPN053

### Auxiliary for control by maintained contact

### Technical properties

#### Configuration

Number of modules	0.5
-------------------	-----

#### Main electrical features

Rated operational voltage Ue	24 / 230 V
Frequency	50 Hz

#### Voltage

Command voltage AC	24 / 230 V
--------------------	------------

#### Electric current

Rated current	2 A
---------------	-----

#### Dimensions

Depth of installed product	64 mm
Height of installed product	85 mm
Width of installed product	8.9 mm

#### Power

Total power loss under IN	0.1 W
---------------------------	-------

#### Connection

Connection cross-sect. flexible conductor	1 / 6mm <sup>2</sup>
Connection cross-sect. rigid cable	1,5 / 10mm <sup>2</sup>
Type of connection	with screw

#### Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	No

#### Use conditions

Operating temperature	-5...40 °C
Storage/transport temperature	-40...80 °C