



EPN053

## Auxiliary for control by maintained contact

### Technical properties

#### Configuration

|                   |     |
|-------------------|-----|
| Number of modules | 0.5 |
|-------------------|-----|

#### Main electrical features

|  |            |
|--|------------|
| Rated operational voltage U <sub>e</sub> | 24 / 230 V |
| Frequency                                | 50 Hz      |

#### Voltage

|                    |            |
|--------------------|------------|
| Command voltage AC | 24 / 230 V |
|--------------------|------------|

#### Electric current

|               |     |
|---------------|-----|
| Rated current | 2 A |
|---------------|-----|

#### Dimensions

|                             |        |
|-----------------------------|--------|
| Depth of installed product  | 64 mm  |
| Height of installed product | 85 mm  |
| Width of installed product  | 8.9 mm |

#### Power

|                                       |       |
|---------------------------------------|-------|
| Total power loss under I <sub>N</sub> | 0.1 W |
|---------------------------------------|-------|

#### Connection

|   |                      |
|---|----------------------|
| Connection cross-sect. flexible conductor | 1 / 6mm <sup>2</sup> |
| Type of connection                        | with screw           |

#### Standards

|                         |           |
|-------------------------|-----------|
| European directive WEEE | concerned |
|-------------------------|-----------|

#### Safety

|               |     |
|---------------|-----|
| REACH conform | Yes |
| RoHS conform  | Yes |
| Halogen free  | No  |

#### Use conditions

|                               |             |
|-------------------------------|-------------|
| Operating temperature         | -5...40 °C  |
| Storage/transport temperature | -40...80 °C |