



EU100

**Compres. control relay**

**Technical properties**

**Architecture**

Fixing mode Din-Rail

**Configuration**

Number of modules 2

**Main electrical features**

Rated operational voltage Ue 230 V

Frequency 50/60 Hz

**Electric current**

Acceptable current rating with AC1 8 A

**Dimensions**

Depth of installed product 60 mm

Height of installed product 85 mm

Length 64 mm

Width of installed product 35 mm

**Power**

Total power loss under IN 4 W

**Measurement**

Voltage measurement range 230 V

**Installation, mounting**

Mounting type din-Rail

**Connection**

Type of contacts 1 changeover

**Settings**

Delay OFF 200 s

**Safety**

Protection index IP IP30

**Use conditions**

Operating temperature -20...55 °C

Storage/transport temperature -40...70 °C