



EU101

**Compres. control relay**

**Technical properties**

**Configuration**

Number of modules	2
-------------------	---

**Main electrical features**

Rated operational voltage Ue	230 V
Frequency	50/60 Hz

**Electric current**

Acceptable current rating with AC1	8 A
------------------------------------	-----

**Dimensions**

Depth of installed product	60 mm
Height of installed product	85 mm
Length	64 mm
Width of installed product	35 mm

**Power**

Total power loss under IN	4 W
---------------------------	-----

**Measurement**

Voltage measurement range	230 V
---------------------------	-------

**Power supply**

Supply voltage	3N, 400/230 V
----------------	---------------

**Installation, mounting**

Mounting type	din-Rail
---------------	----------

**Connection**

Connection cross-sect. flexible conductor	1 / 6mm <sup>2</sup>
Connection cross-sect. rigid cable	1,5 / 10mm <sup>2</sup>
Type of contacts	1 changeover
Type of connection	with screw

**Settings**

Delay OFF	200 s
-----------	-------

**Safety**

REACH conform	Yes
RoHS conform	Yes

**Use conditions**

Operating temperature

-20...55 °C

---

Storage/transport temperature

-40...70 °C