



EU103

control relay current monophased 230V

Technical properties

Configuration

Number of modules	2
-------------------	---

Main electrical features

Rated operational voltage Ue	230 V
Frequency	50/60 Hz

Electric current

Acceptable current rating with AC1	8 A
------------------------------------	-----

Dimensions

Length	64 mm
--------	-------

Power

Total power loss under IN	4 W
---------------------------	-----

Power supply

Supply voltage	230 V
----------------	-------

Installation, mounting

Mounting type	din-Rail
---------------	----------

Connection

Connection cross-sect. flexible conductor	1 / 6mm ²
Connection cross-sect. rigid cable	1,5 / 10mm ²
Type of contacts	1 changeover

Use conditions

Operating temperature	-20...55 °C
Storage/transport temperature	-40...70 °C