



EU300

**control relay triphased phase 400V**

**Technical properties**

**Configuration**

Number of modules	2
-------------------	---

**Main electrical features**

Rated operational voltage Ue	400 V
Frequency	50/60 Hz

**Electric current**

Acceptable current rating with AC1	8 A
------------------------------------	-----

**Dimensions**

Depth of installed product	64 mm
Height of installed product	85 mm
Length	64 mm
Width of installed product	35 mm

**Power**

Total power loss under IN	4 W
---------------------------	-----

**Installation, mounting**

Mounting type	din-Rail
---------------	----------

**Connection**

Connection cross-sect. flexible conductor	1 / 6mm <sup>2</sup>
Connection cross-sect. rigid cable	1,5 / 10mm <sup>2</sup>
Type of contacts	1 changeover

**Use conditions**

Operating temperature	-20...55 °C
Storage/transport temperature	-40...70 °C