



EU300

## control relay triphased phase 400V

### Technical properties

#### Architecture

Fixing mode	Din-Rail
-------------	----------

#### Configuration

Number of modules	2
-------------------	---

#### Main electrical features

Rated operational voltage Ue	400 V
Frequency	50/60 Hz

#### Electric current

Acceptable current rating with AC1	8 A
------------------------------------	-----

#### Dimensions

Depth of installed product	64 mm
Height of installed product	85 mm
Length	64 mm
Width of installed product	35 mm

#### Power

Total power loss under IN	4 W
---------------------------	-----

#### Installation, mounting

Mounting type	din-Rail
---------------	----------

#### Connection

Connection cross-sect. flexible conductor	1 / 6mm <sup>2</sup>
Type of contacts	1 changeover

#### Safety

Protection index IP	IP20
---------------------	------

#### Use conditions

Operating temperature	-20...55 °C
Storage/transport temperature	-40...70 °C