



EU301

Compres. control relay

Technical properties

Architecture

Fixing mode	Din-Rail
-------------	----------

Configuration

Number of modules	2
-------------------	---

Main electrical features

Rated operational voltage Ue	400 V
Frequency	50/60 Hz

Electric current

Acceptable current rating with AC1	8 A
------------------------------------	-----

Dimensions

Depth of installed product	60 mm
Height of installed product	85 mm
Length	64 mm
Width of installed product	35 mm

Power

Total power loss under IN	4 W
---------------------------	-----

Measurement

Voltage measurement range	400 V
---------------------------	-------

Installation, mounting

Mounting type	din-Rail
---------------	----------

Connection

Connection cross-sect. flexible conductor	1 / 6mm ²
Type of contacts	1 changeover
Type of connection	with screw

Settings

Delay OFF	200 s
-----------	-------

Safety

Protection index IP	IP30
---------------------	------

Use conditions

Operating temperature	-20...55 °C
Storage/transport temperature	-40...70 °C