



EU302

control relay compressor triphased 400V

Technical properties

Configuration

Number of modules 2

Main electrical features

Frequency 50/60 Hz

Electric current

Acceptable current rating with AC1 8 A

Dimensions

Length 64 mm

Power

Total power loss under IN 4 W

Measurement

Voltage measurement range 400 V

Power supply

Supply voltage 3N, 400/230 V

Installation, mounting

Mounting type din-Rail

Connection

Connection cross-sect. flexible conductor 1 / 6mm²

Connection cross-sect. rigid cable 1,5 / 10mm²

Type of contacts 1 changeover

Settings

Delay OFF 12 s

Use conditions

Operating temperature -20...55 °C

Storage/transport temperature -40...70 °C