



EU302

control relay compressor triphased 400V

Technical properties

Architecture

Fixing mode Din-Rail

Configuration

Number of modules 2

Main electrical features

Frequency 50/60 Hz

Electric current

Acceptable current rating with AC1 8 A

Dimensions

Length 64 mm

Power

Total power loss under IN 4 W

Measurement

Voltage measurement range 400 V

Installation, mounting

Mounting type din-Rail

Connection

Type of contacts 1 changeover

Settings

Delay OFF 12 s

Safety

Protection index IP IP30

Use conditions

Operating temperature -20...55 °C

Storage/transport temperature -40...70 °C