



EW025\_C

## Industrial contactor 26A-AC3 / coil 220V 50-60Hz

### Technical properties

#### Architecture

Type of pole	3 P
--------------	-----

#### Main electrical features

Rated operational voltage Ue	660 V
Type of supply voltage	AC

#### Voltage

Rated insulation voltage	660 V
DC control voltage	0 V
Command voltage AC	220 V

#### Electric current

Acceptable current rating with AC1	35 A
Rated current	26 A
Thermal rated current outside of housings	35 A
Rated operational current in AC3	26 A

#### Dimensions

Depth of installed product	92 mm
Height of installed product	72 mm
Width of installed product	55 mm

#### Frequency

Frequency	50 to 60 Hz
-----------	-------------

#### Power

Contact rating with 400 V in AC3	38 kW
----------------------------------	-------

#### Endurance

Electric endurance in number of cycles	500000
Number of mechanical operations	5000000

#### Connection

Connection cross-section of input and output with screws, for massive conductors	2.5 / 10 mm <sup>2</sup>
Connection cross section of access and exit with screws, for flexible conductor	2.5 / 10 mm <sup>2</sup>
Type of connection	with screw

#### Equipment

Number of auxiliary contacts as normally closed contact	1
Number of auxiliary contacts as normally open contact	1
Quantity of NC contacts	0
Quantity of NO contacts	3

#### Standards

European directive WEEE	not concerned
-------------------------	---------------

#### Safety

REACH conform	No
RoHS conform	Yes

#### Use conditions

Operating temperature	-20...55 °C
Altitude	2000 m
Storage/transport temperature	-40...80 °C
Relative humidity (without condensation)	45...85 %