



FB6011007030



**Trunking 60x110, grey**

**Technical properties**

**Configuration**

Antibacterial treatment No

**Compatibility**

Device installation compatible format Standard 60mm, CEE, MCBs

**Connectivity**

Trunking coupling without coupler

**Dimensions**

Trunking height 61 mm

Length 2000 mm

Trunking width 110 mm

**Capacity**

Maximum number of cables (Ø 11 mm, 50% fill) 23

Maximum number of cables (Ø 11 mm, 50% fill) 23

**Cover, door**

Lid mounting External

Lid shape loose

Lid width 110 mm

Number of lids mountable 1

**Materials**

Material group plastic

Type of surface treatment untreated

Transparent No

**Installation, mounting**

Base punching With base punching

**Cable**

Internal/useful cross section 5460 mm<sup>2</sup>

**Equipment**

Number of plugable separators 1

Compartment quantity 1 / 2

Cable retainers per meter 2

**Standards**

European directive RoHS

voluntary compliance

**Safety**

REACH conform

No

RoHS conform

Yes

Halogen free

No

Impact strength

IK07

**Use conditions**

Operating temperature

-5...60 °C

**temperatur**

Ambient temperature

-5...65 °C