



FB6011009010



## Trunking 60x110,pure white

### Technical properties

#### Configuration

|                         |    |
|-------------------------|----|
| Antibacterial treatment | No |
|-------------------------|----|

#### Compatibility

|                                       |                          |
|---------------------------------------|--------------------------|
| Device installation compatible format | Standard 60mm, CEE, MCBs |
|---------------------------------------|--------------------------|

#### Connectivity

|                   |                 |
|-------------------|-----------------|
| Trunking coupling | without coupler |
|-------------------|-----------------|

#### Dimensions

|                 |         |
|-----------------|---------|
| Trunking height | 61 mm   |
| Length          | 2000 mm |
| Trunking width  | 110 mm  |

#### Capacity

|                                              |    |
|----------------------------------------------|----|
| Maximum number of cables (Ø 11 mm, 50% fill) | 23 |
| Maximum number of cables (Ø 11 mm, 50% fill) | 23 |

#### Cover, door

|                          |          |
|--------------------------|----------|
| Lid mounting             | External |
| Lid shape                | loose    |
| Lid width                | 110 mm   |
| Number of lids mountable | 1        |

#### Materials

|                           |                       |
|---------------------------|-----------------------|
| RAL colour                | RAL 9010 - Pure white |
| Material                  | PVC                   |
| Material group            | plastic               |
| Type of surface treatment | untreated             |
| Transparent               | No                    |

#### Installation, mounting

|               |                    |
|---------------|--------------------|
| Base punching | With base punching |
|---------------|--------------------|

#### Cable

|                               |          |
|-------------------------------|----------|
| Internal/useful cross section | 5460 mm² |
|-------------------------------|----------|

#### Equipment

|                               |   |
|-------------------------------|---|
| Number of fix dividers        | 0 |
| Number of plugable separators | 1 |

|                           |       |
|---------------------------|-------|
| Compartment quantity      | 1 / 2 |
| Cable retainers per meter | 2     |

#### Standards

|                         |                      |
|-------------------------|----------------------|
| European directive RoHs | voluntary compliance |
|-------------------------|----------------------|

#### Safety

|                     |      |
|---------------------|------|
| Protection index IP | IP30 |
| REACH conform       | No   |
| RoHS conform        | Yes  |
| Halogen free        | No   |
| Impact strength     | IK07 |

#### Use conditions

|                       |            |
|-----------------------|------------|
| Operating temperature | -5...60 °C |
|-----------------------|------------|

#### temperatur

|                     |            |
|---------------------|------------|
| Ambient temperature | -5...65 °C |
|---------------------|------------|