



FB6015007030



## Trunking 60x150, grey

### Technical properties

#### Configuration

Antibacterial treatment No

#### Compatibility

Device installation compatible format Standard 60mm, CEE, MCBs

#### Connectivity

Trunking coupling without coupler

#### Dimensions

Trunking height 61 mm

Length 2000 mm

Trunking width 150 mm

#### Capacity

Maximum number of cables (Ø 11 mm, 50% fill) 31

Maximum number of cables (Ø 11 mm, 50% fill) 31

#### Cover, door

Lid mounting External

Lid shape loose

Lid width 150 mm

Number of lids mountable 1

#### Materials

Colour stone grey

Material group plastic

Type of surface treatment untreated

Transparent No

#### Installation, mounting

Base punching With base punching

#### Cable

Internal/useful cross section 7270 mm<sup>2</sup>

#### Equipment

Number of plugable separators 3

Compartment quantity 1 / 4

Cable retainers per meter 2

**Standards**

---

European directive RoHS	voluntary compliance
-------------------------	----------------------

**Safety**

---

Protection index IP	IP30
---------------------	------

---

Impact strength	IK07
-----------------	------

**Use conditions**

---

Operating temperature	-5...60 °C
-----------------------	------------

**temperatur**

---

Ambient temperature	-5...65 °C
---------------------	------------