



FB6015007030



Trunking 60x150, grey

Technical properties

Configuration

Antibacterial treatment No

Compatibility

Device installation compatible format Standard 60mm, CEE, MCBs

Connectivity

Trunking coupling without coupler

Dimensions

Trunking height 61 mm

Length 2000 mm

Trunking width 150 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill) 31

Maximum number of cables (Ø 11 mm, 50% fill) 31

Cover, door

Lid mounting External

Lid shape loose

Lid width 150 mm

Number of lids mountable 1

Materials

Material group plastic

Type of surface treatment untreated

Transparent No

Installation, mounting

Base punching With base punching

Cable

Internal/useful cross section 7270 mm²

Equipment

Number of plugable separators 3

Compartment quantity 1 / 4

Cable retainers per meter 2

Standards

Approvals	EN50085-2-1
European directive RoHS	voluntary compliance

Safety

REACH conform	No
RoHS conform	Yes
Halogen free	No
Impact strength	IK07

Use conditions

Operating temperature	-5...60 °C
-----------------------	------------

temperatur

Ambient temperature	-5...65 °C
---------------------	------------
