



FB6019007030



## Trunking 60x190, grey

### Technical properties

#### Configuration

Antibacterial treatment	No
-------------------------	----

#### Compatibility

Device installation compatible format	Standard 60mm, CEE, MCBs
---------------------------------------	--------------------------

#### Connectivity

Trunking coupling	without coupler
-------------------	-----------------

#### Dimensions

Trunking height	61 mm
Length	2000 mm
Trunking width	190 mm

#### Capacity

Maximum number of cables (Ø 11 mm, 50% fill)	39
Maximum number of cables (Ø 11 mm, 50% fill)	39

#### Cover, door

Lid mounting	External
Lid shape	loose
Lid width	190 mm
Number of lids mountable	1

#### Materials

Colour	stone grey
Material group	plastic
Type of surface treatment	untreated
Transparent	No

#### Installation, mounting

Base punching	With base punching
---------------	--------------------

#### Cable

Internal/useful cross section	9150 mm <sup>2</sup>
-------------------------------	----------------------

#### Equipment

Number of plugable separators	3
Compartment quantity	1 / 4
Cable retainers per meter	2

**Standards**

European directive RoHS

voluntary compliance

**Safety**

Protection index IP

IP30

Impact strength

IK07

**Use conditions**

Operating temperature

-5...60 °C

**temperatur**

Ambient temperature

-5...65 °C