



FB6019007030



Trunking 60x190, grey

Technical properties

Configuration

Antibacterial treatment	No
-------------------------	----

Compatibility

Device installation compatible format	Standard 60mm, CEE, MCBs
---------------------------------------	--------------------------

Connectivity

Trunking coupling	without coupler
-------------------	-----------------

Dimensions

Trunking height	61 mm
Length	2000 mm
Trunking width	190 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill)	39
Maximum number of cables (Ø 11 mm, 50% fill)	39

Cover, door

Lid mounting	External
Lid shape	loose
Lid width	190 mm
Number of lids mountable	1

Materials

Material group	plastic
Type of surface treatment	untreated
Transparent	No

Installation, mounting

Base punching	With base punching
---------------	--------------------

Cable

Internal/useful cross section	9150 mm ²
-------------------------------	----------------------

Equipment

Number of plugable separators	3
Compartment quantity	1 / 4
Cable retainers per meter	2

Standards

Approvals	EN50085-2-1
European directive RoHS	voluntary compliance

Safety

REACH conform	No
RoHS conform	Yes
Halogen free	No
Impact strength	IK07

Use conditions

Operating temperature	-5...60 °C
-----------------------	------------

temperatur

Ambient temperature	-5...65 °C
---------------------	------------
