



FB80130070301



Trunking 80x130, grey

Technical properties

Configuration

Antibacterial treatment No

Compatibility

Device installation compatible format Standard 60mm, CEE, MCBs

Connectivity

Trunking coupling without coupler

Dimensions

Trunking height 82 mm

Length 2000 mm

Trunking width 130 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill) 33

Maximum number of cables (Ø 11 mm, 50% fill) 33

Cover, door

Lid mounting External

Lid shape loose

Lid width 130 mm

Number of lids mountable 1

Materials

Material group plastic

Type of surface treatment untreated

Transparent No

Installation, mounting

Base punching With base punching

Cable

Internal/useful cross section 8930 mm²

Equipment

Number of plugable separators 3

Compartment quantity 1 / 2

Cable retainers per meter 2

Standards

European directive RoHS

voluntary compliance

Safety

REACH conform

No

RoHS conform

Yes

Halogen free

No

Impact strength

IK07

Use conditions

Operating temperature

-5...60 °C

temperatur

Ambient temperature

-5...65 °C