



FB9923007030



Trunking 99x230, grey

Technical properties

Configuration

Antibacterial treatment	No
-------------------------	----

Compatibility

Device installation compatible format	none
---------------------------------------	------

Connectivity

Trunking coupling	without coupler
-------------------	-----------------

Dimensions

Trunking height	100 mm
Length	2000 mm
Trunking width	230 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill)	77
Maximum number of cables (Ø 11 mm, 50% fill)	77

Cover, door

Lid mounting	External
Lid shape	loose
Lid width	230 mm
Number of lids mountable	1

Materials

Material group	plastic
Type of surface treatment	untreated
Transparent	No

Installation, mounting

Base punching	With base punching
---------------	--------------------

Cable

Internal/useful cross section	19660 mm ²
-------------------------------	-----------------------

Equipment

Number of plugable separators	4
Compartment quantity	1 / 5
Cable retainers per meter	2

Standards

European directive RoHS

voluntary compliance

Safety

REACH conform

Yes

RoHS conform

Yes

Halogen free

No

Impact strength

IK07

Use conditions

Operating temperature

-5...60 °C

temperatur

Ambient temperature

-5...65 °C