



FB9923009010



Trunking 99x230,pure white

Technical properties

Configuration

Antibacterial treatment	No
-------------------------	----

Compatibility

Device installation compatible format	none
---------------------------------------	------

Connectivity

Trunking coupling	without coupler
-------------------	-----------------

Dimensions

Trunking height	100 mm
Length	2000 mm
Trunking width	230 mm

Capacity

Maximum number of cables (Ø 11 mm, 50% fill)	77
Maximum number of cables (Ø 11 mm, 50% fill)	77

Cover, door

Lid mounting	External
Lid shape	loose
Lid width	230 mm
Number of lids mountable	1

Materials

RAL colour	RAL 9010 - Pure white
Material	PVC
Material group	plastic
Type of surface treatment	untreated
Transparent	No

Installation, mounting

Base punching	With base punching
---------------	--------------------

Cable

Internal/useful cross section	19660 mm²
-------------------------------	-----------

Equipment

Number of fix dividers	0
Number of plugable separators	4

Compartment quantity	1 / 5
Cable retainers per meter	2
Standards	
European directive RoHs	voluntary compliance
Safety	
Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Impact strength	IK07
Use conditions	
Operating temperature	-5...60 °C
temperatur	
Ambient temperature	-5...65 °C