



FC114

Back plate, Quadro4, H1050 W370 mm

Technical properties

Architecture

Fixing mode Screwed

Dimensions

Insertion depth 270 mm

Depth of installed product 260 mm

Height of installed product 1050 mm

Width of installed product 370 mm

Built-in width 370 mm

Materials

Colour white

RAL colour RAL 9010 - Pure white

Material Steel

Type of surface treatment Painted

Installation, mounting

Suitable for outdoor use No

Standards

European directive WEEE not concerned

Safety

Protection class isol.class I