



FC118

Back plate, Quadro4, H1650 W370 mm

Technical properties

Architecture

Fixing mode	Screwed
-------------	---------

Dimensions

Insertion depth	270 mm
Depth of installed product	260 mm
Height of installed product	1650 mm
Width of installed product	370 mm
Built-in width	370 mm

Materials

Colour	white
RAL colour	RAL 9010 - Pure white
Material	Steel
Type of surface treatment	Painted

Installation, mounting

Suitable for outdoor use	No
--------------------------	----

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

IK protection code against mechanical impacts	08
Protection class	isol.class I
REACH conform	No
RoHS conform	Yes