



FC118

**Back plate, Quadro4, H1650 W370 mm**

**Technical properties**

**Architecture**

Fixing mode Screwed

**Dimensions**

Insertion depth 270 mm

Depth of installed product 260 mm

Height of installed product 1650 mm

Width of installed product 370 mm

Built-in width 370 mm

**Materials**

Colour white

RAL colour RAL 9010 - Pure white

Material Steel

Type of surface treatment Painted

**Installation, mounting**

Suitable for outdoor use No

**Standards**

European directive WEEE not concerned

**Safety**

Protection class isol.class I