



FC344

Glazed door, Quadro4, H1050 W620 mm

Technical properties

Dimensions

Depth of installed product	51 mm
Height of installed product	1050 mm
Width of installed product	620 mm

Cover, door

Type of door closing	Quarter turn lock
Number of keylock of the door	1
Door type for switch gear cabinet	Lock door
Transparent cover or door	Yes

Materials

Colour	white
RAL colour	RAL 9010 - Pure white
Material	Mixed materials
Type of surface treatment	Painted

Equipment

Quantity of section in width	2
Number of keys	1

Safety

Protection class	isol.class I
------------------	--------------