



FC415

Top and bottom panel, Quadro4, W370 mm, IP40

Technical properties

Dimensions

Insertion depth	270 mm
Depth of installed product	260 mm
Height of installed product	73 mm
Width of installed product	370 mm
Built-in width	370 mm

Materials

Colour	pure white
Colour	white
RAL colour	RAL 9010 - Pure white
Surface appearance	glossy
Type of surface treatment	powder-coated

Installation, mounting

Suitable for outdoor use	No
With cable entry	Yes

Equipment

Quantity of section in width	1
------------------------------	---

Safety

REACH conform	No
RoHS conform	Yes