



FD01A2

Kit, NewVegaD, 150x500mm, with depth-adjustable DIN rail and plain cover

Technical properties

Configuration

Number of modules	24
-------------------	----

Dimensions

Depth of installed product	147 mm
Height of installed product	150 mm
Width of installed product	500 mm

Capacity

Quantity of half modules terminales per rail	40
--	----

Installation, mounting

Quantity of terminal steps in 1/2 modules on kit	40
--	----

Equipment

Number of rows	1
Quantity of steps in height	2