



FD02A2

Kit, NewVegaD, 300x500mm, with depth-adjustable DIN rails and plain cover

Technical properties

Configuration

Number of modules	48
-------------------	----

Dimensions

Depth of installed product	147 mm
Height of installed product	300 mm
Width of installed product	500 mm

Capacity

Quantity of half modules terminales per rail	48
--	----

Materials

Colour	white
RAL colour	RAL 9010 - Pure white

Installation, mounting

Quantity of terminal steps in 1/2 modules on kit	96
--	----

Equipment

Number of rows	2
Quantity of steps in height	4

Safety

REACH conform	No
RoHS conform	Yes
Halogen free	No