



FD22AN

**Enclosure, NewVegaD, 450x550x193mm, 48 modules, surface-mounted, to complete**

## Technical properties

### Configuration

Number of modules	48
-------------------	----

### Main electrical features

Nominal voltage	230/400 V
-----------------	-----------

### Electric current

Rated current	160 A
---------------	-------

### Dimensions

Depth of installed product	193 mm
Internal depth	193 mm
Height of installed product	450 mm
Width of installed product	550 mm
Width in division units	24
Thickness of sidewall material	1 mm

### Cover, door

Number of keylock of the door	0
Cover type	With Notch
Door leave	single
Cover type	none / closed
Transparent cover or door	No

### Materials

Colour	white
RAL colour	RAL 9010 - Pure white
Type of surface treatment	powder-coated

### Installation, mounting

Suitable for outdoor use	No
--------------------------	----

### Settings

Enclosure type	Distributor empty cabinet
----------------	---------------------------

### Equipment

Number of rows	2
Quantity of rails	0
Can be accessorized	Yes
Number of openings for flange plates	2
Extension possible	Yes

Subject to technical modifications

Earthing terminal block	Yes
Neutral terminal block	No
Signal passing door	No

#### Standards

European directive WEEE	not concerned
-------------------------	---------------

#### Safety

Protection class	isol.class II
REACH conform	No
RoHS conform	Yes
Halogen free	No
Fire resistance	-