



FD32AN

Enclosure, NewVegaD, 600x550x193mm, 72 modules, surface-mounted, to complete

Technical properties

Configuration

Number of modules 72

Main electrical features

Nominal voltage 230/400 V

Electric current

Rated current 160 A

Dimensions

Depth of installed product 193 mm

Internal depth 193 mm

Height of installed product 600 mm

Width of installed product 550 mm

Width in division units 24

Thickness of sidewall material 1 mm

Cover, door

Cover type With Notch

Door leave single

Cover type none / closed

Transparent cover or door No

Materials

Colour white

RAL colour RAL 9010 - Pure white

Type of surface treatment powder-coated

Installation, mounting

Suitable for outdoor use No

Settings

Enclosure type Distributor empty cabinet

Equipment

Number of rows 3

Quantity of rails 1

Can be accessorized Yes

Number of openings for flange plates 2

Extension possible Yes

Earthing terminal block Yes

Subject to technical modifications

| | |
|------------------------|----|
| Neutral terminal block | No |
| Signal passing door | No |

Standards

| | |
|-------------------------|---------------|
| European directive WEEE | not concerned |
|-------------------------|---------------|

Safety

| | |
|------------------|---------------|
| Protection class | isol.class II |
| REACH conform | No |
| RoHS conform | Yes |
| Halogen free | No |
| Fire resistance | - |
