



FD62AN

Enclosure, NewVegaD, 1050x550x193mm, 144 modules, surface-mounted, to complete

Technical properties

Functions

Cover with overpressure release No

Configuration

Number of modules 144

Main electrical features

Nominal voltage 230/400 V

Electric current

Rated current 160 A

Dimensions

Depth of installed product 193 mm

Internal depth 193 mm

Height of installed product 1050 mm

Width of installed product 550 mm

Width in division units 24

Thickness of sidewall material 1 mm

Cover, door

Number of keylock of the door 0

Cover type With Notch

Door leave single

Cover type none / closed

Transparent cover or door No

Materials

Colour white

RAL colour RAL 9010 - Pure white

Type of surface treatment powder-coated

Installation, mounting

Suitable for outdoor use No

Settings

Enclosure type Distributor empty cabinet

Equipment

Number of rows 6

Quantity of rails 4

Can be accessorized	Yes
Number of openings for flange plates	2
Extension possible	Yes
Earthing terminal block	Yes
Neutral terminal block	No
Signal passing door	No

Safety

Protection class	isol.class II
REACH conform	No
RoHS conform	Yes
Halogen free	No
Fire resistance	-