



FD72AN

**Enclosure, NewVegaD, 1200x550x193mm, 168 modules, surface-mounted, to complete**

**Technical properties**

**Functions**

Cover with overpressure release No

**Configuration**

Number of modules 168

**Main electrical features**

Nominal voltage 230/400 V

**Electric current**

Rated current 160 A

**Dimensions**

Depth of installed product 193 mm

Internal depth 193 mm

Height of installed product 1200 mm

Width of installed product 550 mm

Width in division units 24

Thickness of sidewall material 1 mm

**Cover, door**

Number of keylock of the door 0

Cover type With Notch

Door leave single

Cover type none / closed

Transparent cover or door No

**Materials**

Colour white

RAL colour RAL 9010 - Pure white

Type of surface treatment powder-coated

**Installation, mounting**

Suitable for outdoor use No

**Settings**

Enclosure type Distributor empty cabinet

**Equipment**

Number of rows 7

Quantity of rails 5

Can be accessorized	Yes
Number of openings for flange plates	2
Extension possible	Yes
Earthing terminal block	Yes
Neutral terminal block	No
Signal passing door	No

**Safety**

Protection class	isol.class II
REACH conform	No
RoHS conform	Yes
Halogen free	No
Fire resistance	-