



FK121

**Steel enclosure, FK, plain door 1900x800x500 mm**

**Technical properties**

**Compatibility**

Suitable for lightning protection No

**Dimensions**

Insertion depth 500 mm

Depth of installed product 500 mm

Internal depth 500 mm

Height of installed product 1900 mm

Width of installed product 800 mm

Thickness of sidewall material 1.2 mm

**Cover, door**

Material thickness cover 1.5 mm

Cover type Closed (plain)

Door leave single

Cover type Door

Transparent cover or door No

**Materials**

Colour light grey

RAL colour RAL 7035 - Light grey

Type of surface treatment powder-coated

**Installation, mounting**

Suitable for outdoor use No

**Equipment**

Number of keys 1

Number of openings for flange plates 2

Extension possible Yes

**Standards**

European directive WEEE not concerned

**Safety**

IK protection code against mechanical impacts IK10

Protection class isol.class I

REACH conform No

Halogen free No

Fire resistance -

