



FK130

Steel enclosure, FK, plain door 1900x1000x400 mm

Technical properties

Compatibility

Suitable for lightning protection	No
-----------------------------------	----

Dimensions

Insertion depth	400 mm
Depth of installed product	400 mm
Internal depth	400 mm
Height of installed product	1900 mm
Width of installed product	1000 mm
Thickness of sidewall material	1.2 mm

Cover, door

Material thickness cover	1.5 mm
Cover type	Closed (plain)
Door leave	single
Cover type	Door
Transparent cover or door	No

Materials

Colour	light grey
RAL colour	RAL 7035 - Light grey
Type of surface treatment	powder-coated

Installation, mounting

Suitable for outdoor use	No
--------------------------	----

Equipment

Number of keys	1
Number of openings for flange plates	2
Extension possible	Yes

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

IK protection code against mechanical impacts	IK10
Protection class	isol.class I
REACH conform	No
Halogen free	No
Fire resistance	-

