



FK130

**Steel enclosure, FK, plain door 1900x1000x400 mm**

**Technical properties**

**Compatibility**

Suitable for lightning protection No

**Dimensions**

Insertion depth	400 mm
Depth of installed product	400 mm
Internal depth	400 mm
Height of installed product	1900 mm
Width of installed product	1000 mm
Thickness of sidewall material	1.2 mm

**Cover, door**

Material thickness cover	1.5 mm
Cover type	Closed (plain)
Door leave	single
Cover type	Door
Transparent cover or door	No

**Materials**

Colour	light grey
RAL colour	RAL 7035 - Light grey
Type of surface treatment	powder-coated

**Installation, mounting**

Suitable for outdoor use No

**Equipment**

Number of keys	1
Number of openings for flange plates	2
Extension possible	Yes

**Standards**

European directive WEEE not concerned

**Safety**

IK protection code against mechanical impacts	IK10
Protection class	isol.class I
REACH conform	No
Halogen free	No
Fire resistance	-

