



FK131

Steel enclosure, FK, plain door 1900x1000x500 mm

Technical properties

Architecture

Fixing mode Floor fastening

Compatibility

Suitable for lightning protection No

Dimensions

Insertion depth 500 mm

Depth of installed product 500 mm

Internal depth 500 mm

Height of installed product 1900 mm

Width of installed product 1000 mm

Thickness of sidewall material 1.2 mm

Cover, door

Material thickness cover 1.5 mm

Cover type Closed (plain)

Door leave single

Cover type Door

Transparent cover or door No

Materials

Colour light grey

Colour light grey

RAL colour RAL 7035 - Light grey

Material metal

Type of surface treatment powder-coated

Installation, mounting

Suitable for outdoor use No

Equipment

Number of keys 1

Number of openings for flange plates 2

Extension possible Yes

Standards

European directive WEEE not concerned

Safety

IK protection code against mechanical impacts	IK10
Protection index IP	IP65
Protection class	isol.class I
Fire resistance	-