



FK134

Steel enclosure, FK, plain door 2100x1000x500 mm

Technical properties

Compatibility

Suitable for lightning protection	No
-----------------------------------	----

Dimensions

Insertion depth	500 mm
Depth of installed product	500 mm
Internal depth	500 mm
Height of installed product	2100 mm
Width of installed product	1000 mm
Thickness of sidewall material	1.2 mm

Cover, door

Material thickness cover	1.5 mm
Cover type	Closed (plain)
Door leave	single
Cover type	Door
Transparent cover or door	No

Materials

Colour	light grey
Colour	light grey
RAL colour	RAL 7035 - Light grey
Material	metal

Installation, mounting

Suitable for outdoor use	No
--------------------------	----

Equipment

Number of keys	1
Number of openings for flange plates	2
Extension possible	Yes

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

Protection class	isol.class I
Fire resistance	-