



FK180

Steel enclosure, FK, plain door 1900x1000x400 mm

Technical properties

Compatibility

Suitable for lightning protection No

Dimensions

Insertion depth 400 mm

Depth of installed product 400 mm

Internal depth 400 mm

Height of installed product 1900 mm

Width of installed product 1000 mm

Thickness of sidewall material 1.2 mm

Cover, door

Material thickness cover 1.5 mm

Cover type Closed (plain)

Door leave single

Cover type Door

Transparent cover or door No

Materials

Colour light grey

Colour light grey

RAL colour RAL 7035 - Light grey

Material metal

Installation, mounting

Suitable for outdoor use No

Equipment

Number of openings for flange plates 2

Extension possible Yes

Standards

European directive WEEE not concerned

Safety

Protection class isol.class I

Fire resistance -