



FK184

**Steel enclosure, FK, plain door 2100x1000x500 mm**

**Technical properties**

**Architecture**

|             |                 |
|-------------|-----------------|
| Fixing mode | Floor fastening |
|-------------|-----------------|

**Compatibility**

|                                   |    |
|-----------------------------------|----|
| Suitable for lightning protection | No |
|-----------------------------------|----|

**Dimensions**

|                                |         |
|--------------------------------|---------|
| Insertion depth                | 500 mm  |
| Depth of installed product     | 500 mm  |
| Internal depth                 | 500 mm  |
| Height of installed product    | 2100 mm |
| Width of installed product     | 1000 mm |
| Thickness of sidewall material | 1.2 mm  |

**Cover, door**

|                           |                |
|---------------------------|----------------|
| Material thickness cover  | 1.5 mm         |
| Cover type                | Closed (plain) |
| Door leave                | single         |
| Cover type                | Door           |
| Transparent cover or door | No             |

**Materials**

|                           |                       |
|---------------------------|-----------------------|
| Colour                    | light grey            |
| Colour                    | light grey            |
| RAL colour                | RAL 7035 - Light grey |
| Material                  | metal                 |
| Type of surface treatment | powder-coated         |

**Installation, mounting**

|                          |    |
|--------------------------|----|
| Suitable for outdoor use | No |
|--------------------------|----|

**Equipment**

|                                      |     |
|--------------------------------------|-----|
| Number of openings for flange plates | 2   |
| Extension possible                   | Yes |

**Standards**

|                         |               |
|-------------------------|---------------|
| European directive WEEE | not concerned |
|-------------------------|---------------|

**Safety**

|   |      |
|---|------|
| IK protection code against mechanical impacts | IK10 |
|---|------|

|                  |              |
|------------------|--------------|
| Protection class | isol.class I |
| REACH conform    | No           |
| Fire resistance  | -            |