



FL102A

**Steel enclosure, Orion.Plus, plain door 300x250x160 mm**

**Technical properties**

**Functions**

Cover with overpressure release	No
---------------------------------	----

**Compatibility**

Suitable for lightning protection	No
-----------------------------------	----

**Electric current**

Rated current	630 A
---------------	-------

**Dimensions**

Depth of installed product	160 mm
Internal depth	160 mm
Height of installed product	300 mm
Width of installed product	250 mm
Thickness of sidewall material	2 mm

**Cover, door**

Material thickness cover	21.5 mm
Type of door closing	lock with male triangular wrench
Interlockable	Yes
Number of keylock of the door	1
Cover type	With Notch
Door leave	single
Cover type	Door
Transparent cover or door	No

**Materials**

Colour	RAL 7035
Colour	light grey
RAL colour	RAL 7035 - Light grey
Material	Steel
Type of surface treatment	powder-coated

**Installation, mounting**

Suitable for outdoor use	No
--------------------------	----

**Equipment**

Number of rows	1
Number of keys	1
Number of openings for flange plates	2

Extension possible	Yes
<b>Standards</b>	
European directive WEEE	not concerned
<b>Safety</b>	
IK protection code against mechanical impacts	IK10
Protection class	isol.class I
REACH conform	No
RoHS conform	Yes
Fire resistance	-