



FL102A

Steel enclosure, Orion.Plus, plain door 300x250x160 mm

Technical properties

Functions

Cover with overpressure release No

Compatibility

Suitable for lightning protection No

Electric current

Rated current 630 A

Dimensions

Depth of installed product 160 mm

Internal depth 160 mm

Height of installed product 300 mm

Width of installed product 250 mm

Thickness of sidewall material 2 mm

Cover, door

Material thickness cover 21.5 mm

Type of door closing lock with male triangular wrench

Interlockable Yes

Number of keylock of the door 1

Cover type With Notch

Door leave single

Cover type Door

Transparent cover or door No

Materials

Colour RAL 7035

Colour light grey

RAL colour RAL 7035 - Light grey

Material Steel

Installation, mounting

Suitable for outdoor use No

Settings

Enclosure type Wall cabinet

Equipment

Number of rows 1

Number of keys 1

Number of openings for flange plates	2
Extension possible	Yes

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

Protection class	isol.class I
Fire resistance	-
