



FL102A



Steel enclosure, Orion.Plus, plain door 300x250x160 mm

Technical properties

Functions

Cover with overpressure release	No
---------------------------------	----

Compatibility

Suitable for lightning protection	No
-----------------------------------	----

Electric current

Rated current	630 A
---------------	-------

Dimensions

Depth of installed product	160 mm
Internal depth	160 mm
Height of installed product	300 mm
Width of installed product	250 mm
Thickness of sidewall material	2 mm

Cover, door

Material thickness cover	21.5 mm
Interlockable	Yes
Number of keylock of the door	1
Cover type	With Notch
Door leave	single
Cover type	Door
Transparent cover or door	No

Materials

Colour	light grey
RAL colour	RAL 7035 - Light grey
Type of surface treatment	powder-coated

Installation, mounting

Suitable for outdoor use	No
--------------------------	----

Settings

Enclosure type	Wall cabinet
----------------	--------------

Equipment

Number of rows	1
Number of keys	1
Number of openings for flange plates	2
Extension possible	Yes

Subject to technical modifications

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

IK protection code against mechanical impacts	IK10
Protection class	isol.class I
REACH conform	No
RoHS conform	Yes
Halogen free	Yes
Fire resistance	-