



FL104A

Steel enclosure, Orion.Plus, plain door 350x300x160 mm

Technical properties

Functions

Cover with overpressure release	No
---------------------------------	----

Configuration

Number of modules	20
-------------------	----

Compatibility

Suitable for lightning protection	No
-----------------------------------	----

Electric current

Rated current	630 A
---------------	-------

Dimensions

Depth of installed product	160 mm
Internal depth	160 mm
Height of installed product	350 mm
Width of installed product	300 mm
Width in division units	10
Thickness of sidewall material	2 mm

Cover, door

Type of door closing	lock with male triangular wrench
Interlockable	Yes
Number of keylock of the door	1
Cover type	Closed (plain)
Door leave	single
Cover type	Cover
Transparent cover or door	No

Materials

Colour	RAL 7035
Colour	light grey
RAL colour	RAL 7035 - Light grey
Material	Steel

Installation, mounting

Suitable for outdoor use	No
--------------------------	----

Settings

Enclosure type	Wall cabinet
----------------	--------------

Equipment

Number of rows	2
Quantity of section in width	0
Number of keys	1
Number of openings for flange plates	2
Extension possible	Yes

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection class	isol.class I
Fire resistance	-