



FL104A

**Steel enclosure, Orion.Plus, plain door 350x300x160 mm**

**Technical properties**

**Functions**

Cover with overpressure release	No
---------------------------------	----

**Configuration**

Number of modules	20
-------------------	----

**Compatibility**

Suitable for lightning protection	No
-----------------------------------	----

**Electric current**

Rated current	630 A
---------------	-------

**Dimensions**

Depth of installed product	160 mm
Internal depth	160 mm
Height of installed product	350 mm
Width of installed product	300 mm
Width in division units	10
Thickness of sidewall material	2 mm

**Cover, door**

Interlockable	Yes
Number of keylock of the door	1
Cover type	Closed (plain)
Door leave	single
Cover type	Cover
Transparent cover or door	No

**Materials**

Colour	light grey
RAL colour	RAL 7035 - Light grey
Type of surface treatment	powder-coated

**Installation, mounting**

Suitable for outdoor use	No
--------------------------	----

**Settings**

Enclosure type	Wall cabinet
----------------	--------------

**Equipment**

Number of rows	2
----------------	---

Quantity of section in width	0
Number of keys	1
Number of openings for flange plates	2
Extension possible	Yes

---

**Safety**

IK protection code against mechanical impacts	IK10
Protection class	isol.class I
REACH conform	No
RoHS conform	Yes
Halogen free	Yes
Fire resistance	-