



FL106A

**Steel enclosure, Orion.Plus, plain door 400x300x160 mm**

**Technical properties**

**Functions**

Cover with overpressure release No

**Compatibility**

Suitable for lightning protection No

**Electric current**

Rated current 630 A

**Dimensions**

Depth of installed product 160 mm

Internal depth 160 mm

Height of installed product 400 mm

Width of installed product 300 mm

Thickness of sidewall material 2 mm

**Cover, door**

Material thickness cover 1.5 mm

Type of door closing lock with male triangular wrench

Interlockable Yes

Cover type With Notch

Door leave single

Cover type Door

Transparent cover or door No

**Materials**

Colour RAL 7035

Colour light grey

RAL colour RAL 7035 - Light grey

Material Steel

**Installation, mounting**

Suitable for outdoor use No

**Settings**

Enclosure type Wall cabinet

**Equipment**

Number of keys 1

Number of openings for flange plates 2

Extension possible No

**Standards**

---

European directive WEEE	not concerned
-------------------------	---------------

**Safety**

---

Protection class	isol.class I
------------------	--------------

---

Fire resistance	-
-----------------	---